


## Adjustable Clevis for Ductile or Cast Iron Pipe Fig. 590SS



**Size Range:** 4" through 12" ductile or cast iron pipe

**Material:** 304 Stainless Steel

**Service:** Recommended for the suspension of stationary ductile iron or cast iron pipe.

**Approvals:** Complies with Federal Specification A-A-1192A (Type 1) WW-H-171-E (Type 1), ANSI/MSS SP-69 and MSS SP-58 (Type 1).

**Installation:** Hanger rod nut above clevis must be tightened securely to assure proper hanger performance.

**Adjustment:** Vertical adjustment without removing pipe may be made from 1<sup>5</sup>/<sub>16</sub>" through 3<sup>3</sup>/<sub>16</sub>", varying with the size of the clevis. Tighten upper nut after adjustment.

**Ordering:** Specify pipe size, figure number and name.

**Note:** Figure 590 typically feature a Figure 260SS Top Component.



**Fig. 590SS: Dimensions (in) • Loads (lbs) • Weight (lbs)**

D.I./C.I. Pipe Size	Max Load		Weight	D.I./C.I. Pipe O.D.	Rod Size A	B	C	E	F	G Width Lower
	450° F	650° F								
4	1,215	1,095	1.64	4.80	5/8	5 3/4	8 3/16	4 3/4	1 5/16	1 1/4
6	1,650	1,485	4.26	6.90	3/4	7 1/8	10 9/16	5 15/16	2 1/4	1 1/2
8	1,700	1,530	6.70	9.05		8 5/8	13 3/16	7 1/2		1 3/4
10	1,750	1,575	9.73	11.10	7/8	10 1/8	15 11/16	8 3/4	2 5/16	2
12	1,850	1,665	13.64	13.20		12 1/16	18 11/16	10 11/16		

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	