

Standard 45° Elbow for Fire Protection Fig. 7051*



 - Available galvanized



Material Specifications

Fabricated Fittings

Ductile Iron conforming to ASTM A536

Coatings

Rust inhibiting paint

Color: Orange (Standard)

Hot Dipped Zinc Galvanized conforming to ASTM A153 (Optional)

Other available options
(Example: RAL3000 or RAL9000 Series)

These fittings are designed to provide minimal pressure drop and uniform strength.

For Listings/Approval Details and Limitations, visit our website at www.asc-es.com or contact an ASC Engineered Solutions™ Sales Representative.


Available as a fabricating fittings.

*When ordering, refer to product as FP7051.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

Standard 45° Elbow for Fire Protection Fig. 7051*



Nominal Size	O.D.	Max. Rated Pressure	Center to End	Approx. Wt. Ea.
In./DN(mm)	In./mm	PSI/bar	In./mm	Lbs./kg
1 ¼ 32	1.660 42.2	300 20.7	1 ¾ 44	0.7 0.3
1 ½ 40	1.900 48.3	300 20.7	1 ¾ 44	0.9 0.4
2 50	2.375 60.3	300 20.7	2 51	1.5 0.7
2 ½ 65	2.875 73.0	300 20.7	2 ¼ 57	1.9 0.9
3 80	3.500 88.9	300 20.7	2 ½ 64	3.3 1.5
4 100	4.500 114.3	300 20.7	3 76	5.4 2.4
5 125	5.563 141.3	300 20.7	3 ¼ 83	9.0 4.1
6 150	6.625 168.3	300 20.7	3 ½ 89	11.2 5.1
8 200	8.625 219.1	300 20.7	4 ¼ 108	19.8 9.0

Note:

Additional sizes available, see Gruvlok Catalog or contact an ASC Engineered Solutions Representative.



asc-es.com

Building connections that last™