

Fig. 595 Socket Clamp for Ductile Iron or Cast Iron Pipe Fig. 594 Socket Clamp Washer

Fig. 595 (Formerly Afcon Fig. 850)

Socket Clamp for Ductile Iron or Cast Iron Pipe

Size Range: 4" through 24"

Material: Two carbon steel half bands and four bolts and nuts.

Finish: Plain or Hot-Dip Galvanized with Zinc Plated Bolts & Nuts

Service: Clamps ductile or cast iron mechanical joint piping or mechanical joint or socket joint fittings together to prevent separation or distortion of pipe line under excessive water pressure.

Approvals: Complies with Federal Specification A-A-1192A (Type 8), ANSI/MSS SP-69 and MSS SP-58 (Type 8). Complies with the requirements of the National Fire Protection Association Standard NFPA-24 for Outside Protection.

Ordering: Specify pipe size, figure number, name and finish.





Fig. 594


Socket Clamp Washer

Two cast iron or steel washers, Fig. 594, are used with each Fig. 595 socket clamp and these must be ordered separately.

Ordering: Specify washer size, figure number, name and finish.



Plug Strap for Bell End of Pipe



Pipe Anchor

Fig. 595, Fig. 594: Dimensions (in) • Loads (lbs) • Weight (lbs)

D.I./C.I. Pipe Size	Max Test Pressure (psi)	Force* On Clamp	Weight		D.I.P. O.D.	B	D Width	Bolt Dia. E	F	T	Fig. 594 Washer Rod Dia.
			Fig. 595 Clamp	Fig. 594 Washer							
4		4,550	12.8		4.80	14 ⁵ / ₈			9 ⁵ / ₈		
6		9,340	14.6	1.1	6.90	16 ⁷ / ₈	2	5/8	11 ¹ / ₈	5/8	3/4
8	250	16,080	23.6		9.05	19 ¹ / ₈			14 ¹ / ₈		
10		24,180	29.3	1.7	11.10	21 ³ / ₈	2 1/2	3/4	16 ⁵ / ₈	3/4	1
12		34,230	40.3		13.20	25 ⁵ / ₈			19 ⁵ / ₈		
14	120	22,200	53.9	2.7	15.80	28 ³ / ₄	3	7/8	22 ³ / ₈		
16	115	27,760	76.5		17.40	31 ³ / ₈		1	25 ³ / ₈	1 1/8	1 1/4
18	100	23,900	94.3	4.3	19.50	35 ⁵ / ₈	4	1 1/4	28 ⁷ / ₈		
20	75	27,500	109.8		21.60	37 ³ / ₄	4 1/2		30 ¹ / ₂		1 3/8
24	50	26,200	148.6	5.8	25.80	44 ¹ / ₄	5	1 1/2	36	1 1/4	1 1/2

*Refers to Hydrostatic Test

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	