



## Steel Washer Plate

**Fig. 60 (Formerly Afcon Fig. 962)**



### Material Specifications

**Size Range**

3/8" through 3 3/4"

**Material**

Carbon Steel

**Finish**

- Plain
- Hot-Dip Galvanized

**Service**

A heavy duty washer plate used on top of channels or angles for supporting pipe with rods or U-bolts.

**Maximum Temperature**


Plain 750° F, Galvanized 450° F

**Ordering**

Specify rod size, figure number, name and finish.

### Dimensions (In) - Load (Lbs) - Weight (Lbs)

Rod Size A	Weight	Max Load		C x C x D Size of Stock	Hole Diameter H
		650° F	750° F		
In.	Lbs.	Lbs.	Lbs.	In.	In.
3/8	0.6	730	572	3 x 3 x 1/4	1/2
1/2	0.6	1,350	1,057		5/8
5/8	0.9	2,160	1,692	4 x 4 x 3/8	3/4
3/4	1.6	3,230	2,530		7/8
7/8	2.2	4,480	3,508	4 x 4 x 1/2	1
1	2.1	5,900	4,620		1 1/4
1 1/4	3.3	9,500	7,440	5 x 5 x 1/2	1 1/2
1 1/2	4.8	13,800	10,807		1 3/4
1 3/4	4.7	18,600	14,566	5 x 5 x 3/4	2
2	4.5	24,600	19,265		2 1/4
2 1/4	6.6	32,300	25,295	6 x 6 x 3/4	2 1/2
2 1/2	6.4	39,800	31,169		2 3/4
2 3/4	6.2	49,400	38,687	7 x 7 x 3/4	3
3	5.9	60,100	47,066		3 1/4
3 1/4	5.6	71,900	56,307		3 1/2
3 1/2	8.1	84,700	66,331		3 3/4
3 3/4	7.8	98,500	77,139		4



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	