
Fig. 7068P Cross Fig. 7069P 45° Lateral Fig. 7071P 90° True Wye



Gruvlok plain-end fittings are manufactured to provide minimum pressure drop and uniform flow. Fittings are designed for use with the Fig. 7005 Roughneck Couplings only.

Gruvlok plain-end fittings are available in sizes through 8" nominal pipe size in a variety of styles. Depending on size and configuration, fittings are either segment-welded steel or forged steel.

Fittings are normally coated with a rust inhibiting paint. Other coatings including Hot Dipped Zinc Galvanizing, are available.

Material Specifications

Engineered Solutions

Segment Welded Steel Fittings

Sizes 2" - 4" Carbon Steel pipe conforming to ASTM A 53, Type "F"; Sizes 5" - 8"; Carbon Steel pipe conforming to ASTM A 53, Type "E" or "S", Grade "B".

Steel Fittings

Forged Steel conforming to ASTM A 106.

Adapter Flanges

Class 150 – Carbon Steel conforming to ANSI B16.5 Class 300 – Carbon Steel conforming to ANSI B16.5

Fitting Size

i itting oizo						
Nominal Size	0.D.					
In./DN(mm)	In./mm					
2	2.375					
50	60.3					
21/2	2.875					
65	73.0					
3	3.500					
80	88.9					
31/2	4.000					
90	101.6					
4	4.500					
100	114.3					
5	5.563					
140	141.3					
6	6.625					
150	168.3					
8	8.625					
200	219.1					

Note:

The Fitting Size Chart is used to determine the O.D. of the pipe that the fittings is to be used with. Gruvlok Fittings are identified by either the Nominal size in inches or the Pipe O.D. In./mm.




PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	


Gruvlok® Plain-End Fittings



Fig. 7068P Cross










Fig. 7071P 90° True Wye

Nominal Size	0.D.	Center to End	Approx. Wt. Ea.	Nominal Size	0.D.	Center to Long End	Center to Short End	Approx. Wt. Ea.	Nominal Size	0.D.	Center to Long End	Center to Short End	Approx. Wt. Ea.
In./DN(mm)	In./mm	In./mm	Lbs./kg	In./DN(mm)	In./mm	In./mm	In./mm	Lbs./kg	In./DN(mm)	In./mm	In./mm	In./mm	Lbs./kg
2	2.375	41/4	4.4	2	2.375	7 1/4	23/4	5.1	2	2.375	4 1/4	23/4	3.5
50	60.3	108	2.0	50	60.3	184	70	2.3	50	60.3	108	70	1.6
21/2	2.875	43/4	7.8	21/2	2.875	7 3/4	3	9.5	21/2	2.875	43⁄4	3	6.2
65	73.0	121	3.5	65	73.0	197	76	4.3	65	73.0	121	76	2.8
3	3.500	51/8	10.7	3	3.500	83⁄4	31⁄4	12.8	3	3.500	51/8	31/4	8.5
80	88.9	130	4.9	80	88.9	222	83	5.8	80	88.9	130	83	3.9
4	4.500	51/8	17.0	4	4.500	103⁄4	33/4	22.2	4	4.500	51/8	33/4	14.0
100	114.3	149	7.7	100	114.3	273	95	10.1	100	114.3	149	95	6.4
5	5.563	67⁄8	26.7	5	5.563	123⁄4	4	38.0	5	5.563	67⁄8	4	21.6
125	141.3	175	12.1	125	141.3	324	102	17.2	125	141.3	175	102	9.8
6	6.625	7 5/8	37.7	6	6.625	14	41/2	54.0	6	6.625	7 5/8	41/2	31.2
150	168.3	194	17.1	150	168.3	356	114	24.5	150	168.3	194	114	14.2
8	8.625	10	74.6	8	8.625	18	6	92.0	8	8.625	10	6	53.6
200	219.1	254	33.8	200	219.1	457	152	41.7	200	219.1	254	152	24.3



asc-es.com

Building connections that last "