Rigidlok Coupling Fig. 7401*



The Fig. 7401 Rigidlok Coupling utilizes a technologically advanced housing design that conforms to and grips the pipe.

Coupling installation is fast and easy, remove only one nut and swing the housing over the gasket and into the grooves. The exclusive Guidelok feature automatically separates the grooved pipe ends and guides the coupling into position as the bolts are tightened. Precisely sized and oriented tines in the housing key section firmly grip the pipe. The combination of these designed in features produce a secure, rigid pipe joint connection.

The Figure 7401 Rigidlok Coupling with a Pre–Lubricated Grade "E" EPDM, Type "A" gasket (coupling is easily identified by purple nuts) is intended for use in fire protection systems installed in accordance with NFPA Standard 13 "Sprinkler Systems."

For Listings/Approval Details and Limitations, visit our website at www.asc-es.com or contact an ASC Engineered Solutions[™] Sales Representative.

*When ordering, refer to product as FP7401.



Material Specifications

Housing

Bolts

Ductile Iron conforming to ASTM A536, Grade 65-45-12

SAE J429, Grade 5, Zinc Electroplated (Standard)

Heavy Hex Nuts

ASTM A563, Grade A, Zinc Electroplated, Violet Dyed (Standard)

Coatings

Rust inhibiting paint Color: Orange (Standard) Hot Dipped Zinc Galvanized (Optional)

Lubrication

Standard Gruvlok

Gruvlok Xtreme

Gaskets

Properties as designated in accordance with ASTM D2000

Pre-Lubricated **Grade "E" EPDM**, Type A C-Style Gasket (Violet color code) -40°F to 150°F (Service Temperature Range) (-40°C to 66°C)

Recommended for wet and dry (oil free air) fire protection sprinkler systems. For freezing conditions, Gruvlok Xtreme Lubricant is required.

Grade "EP" EPDM Flush Gap Gasket (Green color code)

-40°F to 230°F (Service Temperature Range) (-40°C to 110°C)


Recommended for wet and dry (oil free air) fire protection sprinkler systems. For freezing conditions, Gruvlok Xtreme Lubricant is required.



PROJECT INFORMATION	APPROVAL STAMP				
Project:	Approved				
Address:	Approved as noted				
Contractor:	Not approved				
Engineer:	Remarks:				
Submittal Date:					
Notes 1:					
Notes 2:					



Rigidlok Coupling **Fig. 7401***



Nominal Size	Pipe 0.D.		Max. End	Max. End Range of Pipe End		Coupling Dimensions		Coupling Bolts		Approx.
			Load	Separation	х	Y	Z	Qty.	Size	Wt. Ea.
In./DN(mm)	In./mm	PSI/bar	Lbs./kN	In./mm	In./mm	In./mm	In./mm		In./mm	Lbs./kg
11⁄2	1.900	750	2,126	0-1/32	3	51%	1%	2	³⁄8 x 2¹⁄4	1.8
40.0	48.3	51.7	9.46	0-0.79	76	130	48		M10 x 57	0.8
2	2.375	750	3,323	0-1/32	31⁄2	5⁵%	1%	2	³⁄8 x 2¹⁄2	2.4
50.0	60.3	51.7	14.78	0-0.79	89	143	48		M10 x 63	1.1
2½	2.875	750	4,869	0-1/32	4	61⁄8	1%	2	³⁄8 x 2¹⁄2	2.9
65.0	73.0	51.7	21.66	0-0.79	102	156	48		M10 x 63	1.3
3 O.D.	2.996	750	5,207	0- ¹ / ₃₂	4 ¹ / ₈	6 ¹ / ₈	1 ⁷ / ₈	2	³ / ₈ x 2 ¹ / ₂	3.4
76.1	76.1	51.7	23.52	0-0.79	105	156	48		M10 x 63	1.5
3	3.500	750	7,216	0-1/32	4¾	71⁄4	17⁄8	2	<mark>1⁄2 x 3</mark>	3.6
80.0	88.9	51.7	32.10	0-0.79	121	184	48		M12 x 76	1.6
4	4.500	750	11,928	0-³/32	5%	8¾	21/8	2	<mark>1⁄2 x 3</mark>	5.0
100.0	114.3	51.7	53.06	0-2.38	149	213	54		M12 x 76	2.3
5½ O.D.	5.500	750	17,819	0- ³ / ₃₂	7	9 ³ / ₄	2 ¹ / ₈	2	⁵ / ₈ x 3 ¹ / ₂	6.9
139.7	139.7	51.7	79.26	0-2.38	178	248	54		M16 x 85	3.1
5	5.563	750	18,229	0-³/₃₂	7	10	21/8	2	⁵⁄8 x 3¹⁄2	6.9
125.0	141.3	51.7	81.09	0-2.38	178	254	54		M16 x 85	3.1
6½ 0.D.	6.500	750	24,887	0- ³ / ₃₂	8	11	2 ¹ / ₈	2	⁵ / ₈ x 3 ¹ / ₂	7.6
165.1	165.1	51.7	110.70	0-2.38	203	279	54		M16 x 85	3.4
6	6.625	750	25,854	0-³/32	81⁄8	11 ⅓	21⁄8	2	⁵⁄8 x 3¹⁄2	7.9
150.0	168.3	51.7	115.00	0-2.38	206	283	54		M16 x 85	3.6
8	8.625	600	35,056	0-³/32	10½	141⁄8	2⁵⁄8	2	3⁄4 x 41⁄2	15.9
200.0	219.1	41.4	155.94	0-2.38	267	359	67		M20 x 110	7.2
10	10.750	500	45,381	0-³/₃₂	12 %	17½	2⁵⁄8	2	1 x 6	25.6
250.0	273.1	34.5	201.87	0-2.38	327	445	67		M24 x 150	11.6
12	12.750	400	51,070	0-³/32	15	19½	2⁵⁄8	2	<mark>7∕≋ x 6</mark>	30.5
300.0	323.9	27.6	227.17	0-2.38	381	495	67		M22 x 150	13.8

Note:

Range of Pipe End Separation values are for roll grooved pipe and may be doubled for cut groove pipe.

▲ - Working Pressure Ratings are for reference only and based on Sch. 40 pipe.

WARNING: For dry pipe systems and freezer applications lubrication of the gasket is required, Gruvlok Xtreme Lubricant is required.



asc-es.com

Building connections that last "