


## Standard Tee for Fire Protection Fig. 7060S\*



 - Available galvanized



### Material Specifications

#### Fabricated Fittings

Ductile Iron conforming to ASTM A536

#### Coatings

Rust inhibiting paint

Color: Orange (Standard)

Hot Dipped Zinc Galvanized

conforming to ASTM A153 (Optional)

Other available options

(Example: RAL3000 or RAL9000 Series)

These fittings are designed to provide minimal pressure drop and uniform strength.


For Listings/Approval Details and Limitations, visit our website at [www.asc-es.com](http://www.asc-es.com) or contact an ASC Engineered Solutions™ Sales Representative.

\*When ordering, refer to product as FP7060S.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

## Standard Tee for Fire Protection Fig. 7060S\*



Nominal Size	O.D.	Max. Rated Pressure	Center to End	Approx. Wt. Ea.	Nominal Size	O.D.	Max. Rated Pressure	Center to End	Approx. Wt. Ea.
In./DN(mm)	In./mm	PSI/bar	In./mm	Lbs./kg	In./DN(mm)	In./mm	PSI/bar	In./mm	Lbs./kg
1	1.315	300	2¼	0.9	5½ O.D.	5.500	300	5½	16.1
25	33.4	20.7	57	0.4	139.7	139.7	20.7	140	7.3
1¼	1.660	300	2¾	1.5	5	5.563	300	5½	16.2
32	42.2	20.7	70	0.7	125	141.3	20.7	140	7.3
1½	1.900	300	2¾	1.8	6½ O.D.	6.500	300	6½	24.4
40	48.3	20.7	70	0.8	165.1	165.1	20.7	165	11.1
2	2.375	300	3¼	2.4	6	6.625	300	6½	25.7
50	60.3	20.7	83	1.1	150	168.3	20.7	165	11.7
2½	2.875	300	3¾	4.0	8	8.625	300	7¾	41.1
65	73	20.7	95	1.8	200	219.1	20.7	197	18.6
3 O.D.	2.996	300	4	4.6	10	10.750	300	9	74.5
76.1	76.1	20.7	101	2.1	250	273.1	20.7	229	33.8
3	3.500	300	4¼	5.8	12	12.750	300	10	94.7
80	88.9	20.7	108	2.6	300	323.9	20.7	254	43.0
4	4.500	300	5	10.3					
100	114.3	20.7	127	4.7					

**Note:**

Additional sizes available, see Gruvlok Catalog or contact an ASC Engineered Solutions™ Representative.



asc-es.com

Building connections that last™