

**Standpipe Tee**  
**Fig. 7065**



## Material Specifications

### Fabricated Fittings

Carbon Steel, Schedule 40, conforming to ASTM A53, Grade B

### Coatings

Rust inhibiting paint

Color: Orange (Standard)

Hot Dipped Zinc Galvanized conforming to ASTM A153 (Optional)

Other available options

(Example: RAL3000 or RAL9000 Series)


These fittings are designed to provide minimal pressure drop and uniform strength.

For Listings/Approval Details and Limitations, visit our website at [www.asc-es.com](http://www.asc-es.com) or contact an ASC Engineered Solutions™ Sales Representative.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

## Standpipe Tee Fig. 7065



Nominal Size	O.D.	Max. Rated Pressure	Center to End of Run	Center to End of Branch	Approx. Wt. Ea.
In./DN(mm)	In./mm	PSI/bar	In./mm		Lbs./kg
4 x 4 x 2½ 100 x 100 x 65	4.500 114.3	300 20.7	3¼ 83	4 102	7.6 3.4
6 x 6 x 2½ 150 x 150 x 65	6.625 168.3	300 20.7	3¼ 83	5⅞ 130	11.2 5.1



asc-es.com

Building connections that last™