

- Fig. 7060 EG** High Pressure Tee
- Fig. 7662 EG** High Pressure Header Tee
- Fig. 7068 EG** High Pressure Cross




Fig. 7060 EG

Fig. 7662 EG

Fig. 7068 EG

Gruvlok End Guard fittings are fabricated from extra heavy (XS) materials. The groove conforms to Gruvlok End Guard cut grooving specification. These fittings may be used for high pressure systems and where lined or coated fittings are required. Gruvlok EG fittings conform to NACE STD-RP-04-72 (Contact an ASC Engineered Solutions™ Representative with specific service details). End Guard fittings should only be used with Series 7004 Couplings and EG Gasket.

Double groove fittings available, please contact an ASC Engineered Solutions Sales Representative.

## Material Specifications

### Elbows

Extra strong forged steel fittings conforming to ASTM A 234 with welded tangents of schedule 80 steel pipe conforming to ASTM A 106.

### Tees & Crosses

Forged Steel conforming to ASTM A 106.

### Coatings

Rust inhibiting paint – Color: Orange (standard)

Hot Dipped Zinc Galvanized (optional)

Other Colors Available

(IE: RAL3000 and RAL9000)

For other Coating requirements contact an ASC Engineered Solutions Representative.


### Fitting Size

Nominal Size	O.D.
In./DN(mm)	In./mm
1	1.315
25	33.7
1¼	1.660
32	42.4
1½	1.900
40	48.3
2	2.375
50	60.3
2½	2.875
65	73.0
3	3.500
80	88.9
4	4.500
100	114.3
5	5.563
140	141.3
6	6.625
150	168.3
8	8.625
200	219.1



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

**Fig. 7060 EG**  
High Pressure Tee




Nominal Size	O.D.	Center to End	Approx. Wt. Ea.
In./DN(mm)	In./mm	In./mm	Lbs./kg
2	2.375	3¼	3.3
50	60.3	83	1.5
2½	2.875	3¾	5.1
65	73.0	95	2.3
3	3.500	4¼	9.3
80	88.9	108	4.2
4	4.500	5	15.9
100	114.3	127	7.2
6	6.625	6½	38.5
150	168.3	165	17.5
8	8.625	*	*
200	219.1	*	*
10	10.750	*	*
250	273.0	*	*
12	12.750	*	*
300	323.9	*	*

**Note:**


\* Contact an ASC Engineered Solutions Representative for more information.

**Fig. 7662 EG**  
High Pressure Header Tee



Nominal Size	O.D.	Center to End	Approx. Wt. Ea.
In./DN(mm)	In./mm	In./mm	Lbs./kg
2	2.375	6½	4.9
50	60.3	165	2.2
2	2.375	5	3.6
50	60.3	127	1.6

**Fig. 7068 EG**  
High Pressure Cross



Nominal Size	O.D.	Center to End	Approx. Wt. Ea.
In./DN(mm)	In./mm	In./mm	Lbs./kg
2	2.375	3¼	3.9
50	60.3	83	1.8
2½	2.875	3¾	6.8
65	73.0	95	3.1
3	3.500	4¼	11.5
80	88.9	108	5.2
4	4.500	5	19.3
100	114.3	127	8.8
6	6.625	6½	46.0
150	168.3	165	20.9
8	8.625	*	*
200	219.1	*	*
10	10.750	*	*
250	273.0	*	*
12	12.750	*	*
300	323.9	*	*

**Note:**

\* Contact an ASC Engineered Solutions Representative for more information.



asc-es.com

Building connections that last™