



Spacer Clevis

Figs. AS 2601, AS 2623, AS 2627, AS 2631, AS 2631 D, AS 2648, AS 2651, AS 2654, AS 2654A



"Z" Support


AS 2601
GR HG Other



Use With AS 150.
Std Pkg: 25 · Wt/100 pcs: 67 lbs.

Swivel Adapter


AS 2623
EG Other



Use With AS 2622 Beam Clamp.
Load Rating: 300 lbs.
Std Pkg: 50 · Wt/100 pcs: 31 lbs.

Spacer Clevis


AS 2627
EG Other



Std Pkg: 25 · Wt/100 pcs: 24 lbs.

Swing Gate Fixture Hanger

AS 2631
EG Other



Use With AS 200, AS 210, AS 300, AS 400, and AS 500.
Load Rating: 90 lbs.
Std Pkg: 20 · Wt/100 pcs: 27 lbs.

LEGEND:

GR: Powder Coated Supr-Green **EG:** Electro-Galvanized **AL:** Aluminum **HG:** Hot Dipped Galvanized
PL: Plain **SS:** Stainless Steel **ZTC:** Zinc Trivalent Chromium




PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

Spacer Clevis

Figs. AS 2601, AS 2623, AS 2627, AS 2631, AS 2631 D, AS 2648, AS 2651, AS 2654, AS 2654A

Swing Gate Fixture Hanger


AS 2631 D
EG Other



Use With AS 100, AS 150, AS 200BTB, AS 210BTB.
Load Rating: 90 lbs.
Std Pkg: 20 · Wt/100 pcs: 33 lbs.

"U" Support


AS 2648
GR EG Other



Use With AS 150.
Std Pkg: 25 · Wt/100 pcs: 108 lbs.

Beam Clamp

AS 2651
EG Other




	A	Load Rating
AS 2651 T1	3 3/8"	1000
AS 2651 T2	5"	1000

T1 Use With AS 200, AS 210, AS 300, AS 400, AS 500, AS 520.
T2 Use With AS 100, AS 150, and AS 200BTB.
Std Pkg: 25 · Wt/100 pcs: 80 lbs.

Column Attachment

AS 2654 AS 2654 A
GR EG Other



Use AS 2654 With AS 200. Use AS 2654 A With AS 500.
Slip Rating: 800. Column attachments can only be used in pairs.
Std Pkg: 25 pair · Wt/100 pcs: 41 lbs.

LEGEND:

GR: Powder Coated Supr-Green EG: Electro-Galvanized AL: Aluminum HG: Hot Dipped Galvanized PL: Plain
SS: Stainless Steel ZTC: Zinc Trivalent Chromium