


DZR Brass Union Body with Air Vent and Test Point Fig. 92UN



Material Specifications

- 1. Union Nut**
Brass
- 2. Union**
DZR Brass
- 3. Union O-Ring**
EPDM Perox
- 4. Body**
DZR Brass
- 5. Vent**
DZR Brass
- 6. Test Point**
DZR Brass¹

¹ With EPDM Perox gaskets and polypropylene tie

Features

- DZR Brass Union Body with Air Vent and Test Point
- Threaded F or M (ASME B1.20.1 - NPT)
- Solder joint ends (ASME B16.22)
- 400 WOG


Union ends available on following versions

- Threaded M (ASME B1.20.1 - NPT)
- Solder joint ends (ASME B16.22)

Working Conditions


Water (15°F to 260°F)
below 32°F only for water with added anti-freezing fluids
over 212°F only for water with added anti-boiling fluids

For additional information on Gruvlok bag and tag coil kit service, contact an ASC Engineered Solutions Representative.



| PROJECT INFORMATION | APPROVAL STAMP |
|---------------------|-------------------|
| Project: | Approved |
| Address: | Approved as noted |
| Contractor: | Not approved |
| Engineer: | Remarks: |
| Submittal Date: | |
| Notes 1: | |
| Notes 2: | |

DZR Brass Union Body with Air Vent and Test Point Fig. 92UN



| Union Size | N | ØS | C | B | P | AM | AF | AC | UM | UC | HD | HT | Approx. Wt. Each ¹ |
|-------------|-------------|----------------------------|--------------|--------------|--------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------------------------|
| In./mm | In./mm | In./mm | In./mm | In./mm | In./mm | In./mm | In./mm | In./mm | In./mm | In./mm | In./mm | In./mm | Lbs./Kg |
| 1/2 15 | 1/2 15 | 0.627-0.631 15.93-16.03 | 0.55 14.0 | 0.51 13.0 | 0.59 15.0 | 1.7 43.2 | 1.6 40.6 | 1.5 38.1 | 1.4 35.6 | 0.9 22.3 | 1.6 40.6 | 2.2 55.9 | 0.50/0.58 0.23/0.26 |
| 3/4 20 | 3/4 20 | 0.877-0.881 22.28-22.38 | 0.63 16.0 | 0.78 19.8 | 0.74 18.8 | 1.7 43.2 | 1.7 43.2 | 1.7 43.2 | 1.5 38.1 | 1.4 35.6 | 1.6 40.6 | 2.2 55.9 | 0.57/0.64 0.26/0.29 |
| 1 25 | 1 25 | 1.128-1.131 28.65-28.73 | 0.70 17.8 | 0.91 23.1 | 1.00 25.4 | 1.9 48.3 | 1.7 43.2 | 1.9 48.3 | 1.8 45.7 | 1.6 40.6 | 1.9 48.3 | 2.3 58.4 | 0.64/0.84 0.29/0.38 |
| 1 1/4 32 | 1 1/4 32 | 1.378-1.381 35.00-35.08 | 0.73 18.5 | 0.98 24.9 | 1.25 31.8 | 2.0 50.8 | 1.8 45.7 | 2.0 50.8 | 1.9 48.3 | 1.7 43.2 | 2.0 50.8 | 2.5 63.5 | 1.01/1.15 0.46/0.53 |
| 1 1/2 40 | 1 1/2 40 | 1.628-1.632 41.35-41.45 | 0.77 19.6 | 1.10 27.9 | 1.50 38.1 | 2.1 53.3 | 1.8 45.7 | 2.1 53.3 | 2.2 55.9 | 1.9 48.3 | 2.1 53.3 | 2.5 63.5 | 1.59/1.90 0.72/0.86 |
| 2 50 | 2 50 | 2.128-2.132 54.05-54.15 | 0.80 20.3 | 1.35 34.3 | 1.97 50.0 | 2.1 53.3 | 1.8 45.7 | 2.2 55.9 | 2.3 58.4 | 2.1 53.3 | 2.4 61.0 | 2.8 71.1 | 1.90/2.26 0.86/1.03 |

¹ Weight varying in the indicated range depending on the body/union end combination



asc-es.com

Building connections that last™