


Linked Eylet with Stud Figs. AS 203, AS 3281, AS 6075, AS 6024

Linked Eyelet with Stud

AS 203	EG	
Size	Std Pkg	Wt./100 Pcs.
3/8"	100	27.0
1/2"	50	45.0

Max. Load: 610 lbs.
Std Pkg & Wt/100 pcs: See chart above.




Description

Anvil-Strut Hardware, when used in conjunction with Anvil-Strut Channel and Nuts, provides a superior grip between channels and fittings.

Double Conveyor Adjusting Nut

AS 3281 EG



Use for all 15/8" wide Anvil-Strut channels.
Size 3/8", Threads 16
Wt/100 pcs: 175 Lbs

Slotted Hex Head Machine Screw

AS 6075 EG

Size	Std Pkg	Wt./100 Pcs.
1/4" X 3/4"	100	1.7
5/16" X 1"	100	2.6
5/16" X 1 1/4"	100	3.0
5/16" X 1 1/2"	100	3.4
3/8" X 1 1/4"	100	5.3




Std Pkg & Wt/100 pcs: See chart above.

Hex Head Cap Screw

AS 6024 EG

Diameter	Length	Wt./100 Pcs.
1/4"	3/4"	1.3
1/4"	1"	1.7
1/4"	1 1/4"	2.0
1/4"	1 1/2"	2.0
3/8"	3/4"	4.0
3/8"	1"	4.5
3/8"	1 1/4"	5.3
3/8"	1 1/2"	6.1
3/8"	2"	7.6
1/2"	3/4"	8.0
1/2"	1"	9.1
1/2"	1 1/4"	10.0
1/2"	1 1/2"	11.6
1/2"	1 3/4"	13.2
1/2"	2"	14.7



For use with Channel Nuts to secure fittings to channels.

Std Pkg 100 & Wt/100 pcs: See chart above.

LEGEND:

GR: Powder Coated Supr-Green
EG: Electro-Galvanized
PG: Pre-Galvanized
AL: Aluminum
HG: Hot Dipped Galvanized
PL: Plain
SS: Stainless Steel
ZTC: Zinc Trivalent Chromium Stainless Steel (**SS**), Zinc Trivalent Chromium (**ZTC**) and Hot Dipped Galvanized (**HG**) are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	