


C-Clamp with Locknut Fig. 95



Material Specifications

Size Range
3/8" and 1/2"

Material
Carbon Steel

Finish
Plain
Zinc Plated

Service
Designed for fastening flange of "W" and "M" beam. Bottom hole tapped to accommodate hanger rod.

Approvals
Complies with Federal Specification A-A-1192A (Type 23), WW-H-171-E (Type 23), ANSI/MSS SP-69 and MSS SP-58 (Type 23).

Installation
Follow recommended set screw torque values per MSS-SP-69.

Ordering
Specify rod size, figure number, name and finish.

Note
If a retaining clip is desired, you may specify either Fig. 89X or Fig. 89. For length and other ordering information, refer to Fig. 89X and Fig. 89.

Dimensions (In) - Load (Lbs) - Torque (In-Lbs) - Weight (Lbs)

Rod Size A	Set Screw Size	Torque Value	Max Load	B	C	D	Weight	Rod Sized Retaining Clips	
								Fig. 89	Fig. 89X
In.	In.	In.-Lbs.	Lbs.	In.	In.	In.	Lbs.	In.	In.
3/8	3/8	60	230	3/4	2 1/4	2 3/8	0.34	3/8	3/8
1/2	1/2	125	380	3/4	2 1/4	2 3/8	0.40	3/8	1/2



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	