




Channel Fig. AS 520, AS 520EH, AS 520S, AS 520H





Channel Fig. AS 520, AS 520EH, AS 520S, AS 520H





¹³/₁₆" x 1⁵/₈" (20.6 x 41.3mm) 12 Gauge Channel • wt./100 ft. - 135#

Stocked in pre-galvanized, plain, powder coated Supr-Green, in both 10 & 20 ft. lengths. Other materials, finishes & lengths are available upon request.

						P	ropertie	s of Sec	tion							
Catalog	Wt	./Ft.	Area of	Section	X-X Axis Y-Y A								Y Axis			
No.	Lbs.	Kg	Sq. In.	Sq. cm	l in⁴	l cm⁴	S in ³	S cm ³	r in.	r cm	l in4	l cm⁴	S in ³	S cm ³	r in.	r cm
AS 520	1.37	2.0	0.384	2.477	0.032	1.332	0.067	1.098	0.289	0.734	0.139	5.786	0.171	2.802	0.602	1.529
= Moment of Inertia		S = Sect	ion Modulus	r = Radi	ius of Gyrat	ion										

Beam & Column Loads											
			Static Beam L	oad (X–X Axis	Max.	Column Loading Data					
Span or Unbraced	Max	Deflection		Uniform Load	at Deflection	Allowable	Max. Column Load Applied at C.G.				
Height	Allowable Uniform Load	at Uniform Load	Span/180 Deflection	Span/240 Deflection	Span/360 Deflection	Weight of Channel	Load at Slot Face	k=.65	k=.80	k=1.0	k=1.2
In	Lbs	In	Lbs	Lbs	Lbs	Lbs	Lbs	Lbs	Lbs	Lbs	Lbs
12	1,130	0.03	1,130	1,130	1,130	1.4	2,410	8,480	8,280	7,990	7,710
18	750	0.06	750	750	620	2.1	2,270	8,030	7,710	7,090	6,39
24	560	0.11	560	520	350	2.7	2,090	7,510	6,860	5,900	4,91
30	450	0.17	450	340	220	3.4	1,880	6,800	5,900	4,670	3,50
36	380	0.24	310	230	160	4.1	1,680	6,030	4,910	3,500	2,43
42	320	0.33	230	170	110	4.8	1,470	5,220	3,950	2,570	1,79
48	280	0.43	170	130	90	5.5	1,280	4,430	3,080	1,970	1,37
60	230	0.67	110	80	60	6.9	970	2,980	1,970	**	**
72	190	0.97	80	60	40	8.2	760	2,070	1,370	**	**
84	160	1.32	60	40	30	9.6	**	1,520	**	**	**
96	140	1.72	40	30	20	11.0	**	**	**	**	**
108	130	2.18	30	30	20	12.4	**	**	**	**	**
120	110	2.69	30	20	NR	13.7	**	**	**	**	**
144	90	3.88	20	NR	NR	16.5	**	**	**	**	**
168	80	5.28	NR	NR	NR	19.2	**	**	**	**	**
180	80	6.06	NR	NR	NR	20.6	**	**	**	**	**
192	70	6.89	NR	NR	NR	22.0	**	**	**	**	**
216	60	8.72	NR	NR	NR	24.7	**	**	**	**	**
240	60	10.77	NR	NR	NR	27.5	**	**	**	**	**

Bearing Load may limit load ** Not recommended – KL/r exceeds 200

Notes:

1. The beam capacities shown above include the weight of the strut beam. The beam weight must be subtracted from these capacities to arrive at the net beam capacity.

2. Allowable beam loads are based on a uniformly loaded, simply supported beam. For capacities of a beam loaded at midspan at a single point, multiply the beam capacity by 50% and deflection by 80%.

3. The above chart shows beam capacities for strut without holes. For strut with holes, multiply by the following:

S by 90%, H (⁹/₁₆ holes) by 88%, KO by 82%.

4. Refer to the Anvil-Strut Catalog for reduction factors for unbraced lengths.



EH by 88%,



Channel Fig. AS 520, AS 520EH, AS 520S, AS 520H

Beam & Column Loads – Metric												
Span or Unbraced Height		S	tatic Beam L	oad (X–X Axis		Column Loading Data						
	Max Allowable Uniform Load	Deflection at Uniform Load	l	Jniform Load	l at Deflectio	n	Max. Allowable Load at Slot Face	Max. Column Load Applied at C.G.				
			Span/180 Deflection	Span/240 Deflection	Span/360 Deflection	Weight of Channel		k=.65	k=.80	k=1.0	k=1.2	
mm	Kn	mm	Kn	Kn	Kn	Kg	Kn	Kn	Kn	Kn	Kn	
305	5.0	0.8	5.0	5.0	5.0	0.6	10.7	37.7	36.8	35.5	34.3	
457	3.3	1.5	3.3	3.3	2.8	1.0	10.1	35.7	34.3	31.5	28.4	
610	2.5	2.8	2.5	2.3	1.6	1.2	9.3	33.4	30.5	26.2	21.8	
762	2.0	4.3	2.0	1.5	1.0	1.5	8.4	30.2	26.2	20.8	15.6	
914	1.7	6.1	1.4	1.0	0.7	1.9	7.5	26.8	21.8	15.6	10.8	
1,067	1.4	8.4	1.0	0.8	0.5	2.2	6.5	23.2	17.6	11.4	8.0	
1,219	1.2	10.9	0.8	0.6	0.4	2.5	5.7	19.7	13.7	8.8	6.1	
1,524	1.0	17.0	0.5	0.4	0.3	3.1	4.3	13.3	8.8	**	**	
1,829	0.8	24.6	0.4	0.3	0.2	3.7	3.4	9.2	6.1	**	**	
2,134	0.7	33.5	0.3	0.2	0.1	4.4	**	6.8	**	**	**	
2,438	0.6	43.7	0.2	0.1	0.1	5.0	**	**	**	**	**	
2,743	0.6	55.4	0.1	0.1	0.1	5.6	**	**	**	**	**	
3,048	0.5	68.3	0.1	0.1	NR	6.2	**	**	**	**	**	
3,658	0.4	98.6	0.1	NR	NR	7.5	**	**	**	**	**	
4,267	0.4	134.1	NR	NR	NR	8.7	**	**	**	**	**	
4,572	0.4	153.9	NR	NR	NR	9.3	**	**	**	**	**	
4,877	0.3	175.0	NR	NR	NR	10.0	**	**	**	**	**	
5,486	0.3	221.5	NR	NR	NR	11.2	**	**	**	**	**	
6,096	0.3	273.6	NR	NR	NR	12.5	**	**	**	**	**	

Channel Specifications

Materials

Carbon Steel

Channels are formed from high-quality, structural grade carbon steel which has been manufactured in accordance with ASTM A-1011-04-SS Grade 33 (hot rolled), or ASTM 366 (cold rolled), with mechanical properties of 33 ksi minimum yield and 52 ksi minimum tensile strength. The precision roll-forming process by which the channels are formed "cold works" the steel, thereby increasing its mechanical properties.

Stainless Steel

Channels are formed from chromium–nickel stainless steel sheet manufactured in accordance with ASTM A–240 specification, offered in both AISI Type 304 and 316 material to provide protection in varying corrosive conditions.

Aluminum

Extruded aluminum channel is produced from 6063–T6 alloy, and fittings are produced from 5052–H32 alloy, both in accordance with ASTM B–221 specifications. Aluminum is suitable for use in various corrosive environments.

Finishes

Pre-Galvanized

Hot dip, mill galvanized coating produced through a process of continuously passing the steel through a bath of molten zinc. This process is performed in accordance with ASTM A-653. The thickness of the zinc coating conforms with ASTM G-90 which represents a coating thickness of .90 ounces of zinc per square foot. This coating is applied to the steel master coils prior to slitting and fabrication.

Hot Dip Galvanized - Post Fabrication

The finished channel is completely immersed in a bath of molten zinc, resulting in the complete coating of all surfaces of the product, including edges and welds. Strut channels that are hot dip galvanized, have a total coating weight of 3.0 ounces of zinc per square foot in accordance with ASTM A-123 specification. This coating provides superior results in applications calling for prolonged outdoor exposure.

Supr-Green Powder Coating

Strut channels are coated after fabrication with polyester powder finish. This coating is applied using an electrostatic spray process, beginning with cleaning and phosphating, through a bonderite pretreatment process, and ending with oven curing. The resulting finish provides a high quality appearance and durability. Powder Coating is in accordance with ASTM B-117 (standard practice for operating salt spray [fog] apparatus) to 500 hours with less than $\frac{1}{8}$ " scribe creep.

Zinc Trivalent Chromium

The finished channel undergoes a multi-step process consisting of electrogalvanizing, in accordance with ASTM B-633-85, followed by an application of zinc trivalent chromium, which provides the distinctive gold coloration of the finish. All surfaces are coated because the process is performed after fabrication.

PVC

A corrosive resistant PVC (polyvinyl chloride) coating is applied over the completed strut channel. The coating process consists of surface pretreatment, followed by preheating of the part, which is then passed through a fluidized bed of vinyl plastic powder. The powder melts onto the heated channel forming a smooth coating which undergoes a final heat curing.