


# ABZ 6000 Series

## Triple Offset High Performance

### Pressure/Temperature Rating (A351 Gr. CF8M)



**Maximum applicable Temperature for Stem & Seat:**

**STEM:**  
 17-4PH: -100°F ~ 800°F; Duplex: -60°F ~ 800°F; Monel: -425°F ~ 900°F; Nitronic 50: -325°F ~ 950°F; Hastelloy C: -20°F ~ 1000°F; Inconel 718: -425°F ~ 1500°F

**SEAT:**  
 316SS: -425°F ~ 900°F; 316SS/Graphite: -425°F ~ 1000°F; 316SS/Stellite: -425°F ~ 1200°F; Inconel/Graphite: -325°F ~ 1500°F