# SPF/Anvil® Grooved Fittings





ASC Engineered Solutions™ Sales Representative.

For Listings/Approval Details and Limitations, visit our website at www.asc-es.com or contact an

## **Material Specifications**

### **Cast Fittings**

Ductile Iron conforming to ASTM A536, Grade 65-45-12

#### Finish

Rust inhibiting paint Color: Orange (standard) Hot Dipped Zinc Galvanized conforming to ASTM A153 (optional) Other available options

Example: RAL3000 or RAL9000 Series




PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

# SPF/Anvil® Grooved Fittings



## 90° Elbow **Fig. E-1**



Nominal Size	O.D.	Max. Working Pressure	Center to End	Approx. Wt. Ea.
In./DN(mm)	In./mm	PSI/bar	In./mm	Lbs./kg
1	1.315	300	21/4	0.6
25	33.4	20.7	57	0.3
11/4	1.660	300	23/4	0.8
32	42.2	20.7	70	0.4
11/2	1.900	300	23/4	1.1
40	48.3	20.7	70	0.5
2	2.375	300	31/4	1.5
50	60.3	20.7	83	0.7
21/2	2.875	300	33/4	2.5
65	73.0	20.7	95	1.1
3	3.500	300	41/4	4.2
80	88.9	20.7	108	1.9
4	4.500	300	5	6.7
100	114.3	20.7	127	3.0
5	5.563	300	5½	11.9
125	141.3	20.7	140	5.4
6	6.625	300	61/2	17.3
150	168.3	20.7	165	7.9
8	8.625	300	73/4	32.2
200	219.1	20.7	197	14.6
10	10.750	300	9	54.1
250	273.1	20.7	229	24.5
12	12.750	300	10	70.0
300	323.9	20.7	254	31.8



asc-es.com