


AS 2601 "Z" Support

Figs. AS 2601, AS 611, AS 609, AS 756, AS 3060,

AS 612, AS 711, AS 928




Description

Anvil–Strut "Z" Supports are designed to fit with all Anvil–Strut $1^5/8$ " wide channels. Unless otherwise noted, Anvil–Strut "Z" Supports are manufactured from 1/4" thick carbon steel, $1^5/8$ " wide, all holes are 9/16" diameter, spaced $1^7/8$ " on center and $1^3/16$ " from the end.

"Z" Support


AS 611 EG, GR, ZTC



Use with AS 200, AS 210, & AS 500 BTB Std Pkg 50 – Wt/100 pcs: 54 Lbs.

2-Hole Offset "Z" Support

AS 609 EG, GR



Std Pkg 25 - Wt/100 pcs: 38 Lbs.

Page notes unless otherwise specified: 1/4" thick, 15/8" wide, holes 9/16" diameter, spaced 17/8" on center and 13/16" from end.

LEGEND:

GR: Powder Coated Supr-Green **EG**: Electro-Galvanized **PG**: Pre-Galvanized **AL**: Aluminum **HG**: Hot Dipped Galvanized **PL**: Plain **SS**: Stainless Steel **ZTC**: Zinc Trivalent Chromium Stainless Steel **(SS)**, Zinc Trivalent Chromium **(ZTC)** and Hot Dipped Galvanized **(HG)** are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.




PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	



AS 2601 "Z" Support Figs. AS 2601, AS 611, AS 609, AS 756, AS 3060, AS 612, AS 711, AS 928

"Z" Support


AS 756 EG, GR, ZTC



Use with AS 100, AS 200 BTB, & AS 210 BTB Std Pkg 25 - Wt/100 pcs: 70 Lbs.

Offset Connector


AS 3060 EG, GR



Α	Wt./100 Pcs.			
4"	77			
5"	95			
6"	98			
7"	105			
8"	120			

Std Pkg 25 - Wt/100 pcs: See chart above.

"Z" Support



AS 612	EG,	GR	
AS 711	EG,	GR	
AS 928	EG,	GR,	ZTC
AS 2601	EG,	GR	

Catalog No.	Α	Std. Pkg	Wt./100 Pcs.	Use With
AS 612	1"	50	50	AS 400
AS 2601	27/16"	25	66	AS 150
AS 711	13/8"	25	53	AS 300
AS 928	13/16"	50	47	AS 500 & AS 520

Std Pkg & Wt/100 pcs: See chart above.

Page notes unless otherwise specified: 1/4" thick, 15/8" wide, holes 9/16" diameter, spaced 17/8" on center and 13/16" from end.

LEGEND:

GR: Powder Coated Supr-Green **EG**: Electro-Galvanized **PG**: Pre-Galvanized **AL**: Aluminum **HG**: Hot Dipped Galvanized **PL**: Plain **SS**: Stainless Steel **ZTC**: Zinc Trivalent Chromium Stainless Steel **(SS)**, Zinc Trivalent Chromium **(ZTC)** and Hot Dipped Galvanized **(HG)** are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.

