


Support with Threaded Rod Extension and Channel **HBS- CE - Extension Series, PG, HG**



HBS-CE-Extension Series is perfect for supporting natural gas and refrigeration piping systems, cable tray, electrical conduit, multiple lines, HVAC equipment and many other applications.

The HBS-CE-Extension is UV resistant and suitable for installation on most types of roofing material or other flat surfaces.

Roof supports come pre-assembled.

Specifications: HBS-CE

Two H–Block Bases and Threaded Rod Riser with: $^{13}/\!\!\!\!/_{16}$ " H–164 Channel, or 15%" H–132 Channel

Material: 100% recycled rubber, UV resistant

HBS-CE-Extension Series Support with Threaded Rod Extension and Channel

Model No.	Height	Width	Strut Length	Strut Size	Base Length	Weight (Lbs)	Uniform Load Capacity (Lbs)*
HBS-CE10-8-H-164-PG	8" (203 mm)	5" (127 mm)	9.312" (237 mm)	¹³ / ₁₆ " H-164	10 ⁷ /8" (276mm)	6.89	1,000*
HBS-CE10-12-H-164-PG	12" (305 mm)					7.34	1,000*
HBS-CE24-16-H-132-PG	16" (406 mm)		24.000" (610 mm)	1⁵⁄₃" H–132	26" (660mm)	15.85	1,700*

*This load is only for the capacity of the components in this assembly. Please consult roofing manufacturer or engineer for roof load capacity

LEGEND:

PG: Pre-Galvanized HG: Hot Dipped Galvanized

Pricing is located in the ASC Engineered Solutions™ H–Block price book.

PROJECT INFORMATION	APPROVAL STAMP	
Project:	Approved	
Address:	Approved as noted	
Contractor:	Not approved	
Engineer:	Remarks:	
Submittal Date:		
Notes 1:		
Notes 2:	_	