


## Light Duty Copper Tubing Riser Clamp Fig. 008CTG



**Size Range:** ½" through 6" CTS

**Material:** Carbon Steel

**Finish:** Epoxy coated

**Service:** Recommended for the suspension of stationary copper tube.

**Maximum Temperature:** 450° F

**Approvals:** MSS SP-58 (Type-8)

**Installation:** Clamp is to be fitted and bolted below a coupling or hub. Bolt torques should be per industry standards. Clamp is designed for standard copper tube O.D. and this must be considered in sizing the riser for other types of piping.

**Ordering:** Nominal pipe size and figure number.

**Notes:**

- For U.S. domestic product see Figure CT-121 copper tubing riser clamp.

**Fig. 008CTG: Dimensions (in) Loads (lbs)**

Pipe Size	Max Load	Length
½	150	8½
¾	150	9¼
1	150	9 <sup>5</sup> / <sub>16</sub>
1¼	150	9½
1½	150	9 <sup>5</sup> / <sub>8</sub>
2	150	10 <sup>7</sup> / <sub>16</sub>
2½	150	11 <sup>3</sup> / <sub>16</sub>
3	200	11 <sup>15</sup> / <sub>16</sub>
4	250	12½
6	480	15 <sup>3</sup> / <sub>16</sub>



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	