


Two Wheel Trolley

Fig. AS 2521, AS 2522, AS 2528, AS 2528-1




Description

Anvil-Strut Trolleys and Accessories are designed to fit Anvil-Strut 1 5/8" wide channels.

Trolley Beam Standard Support


AS 2528 EG, GR



Std Pkg 10 - Wt/100 pcs: 107 Lbs.

Trolley Beam Joint Support

AS 2528-1 EG, GR



Std Pkg 10 - Wt/100 pcs: 233 Lbs.

LEGEND:

GR: Powder Coated Supr-Green **EG:** Electro-Galvanized **PG:** Pre-Galvanized **AL:** Aluminum
HG: Hot Dipped Galvanized **PL:** Plain **SS:** Stainless Steel **ZTC:** Zinc Trivalent Chromium
 Stainless Steel (SS), Zinc Trivalent Chromium (ZTC) and Hot Dipped Galvanized (HG) are specialty finishes.
 Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.




PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

Two Wheel Trolley Fig. AS 2521, AS 2522, AS 2528, AS 2528-1

Two Wheel Trolley


AS 2521 EG



Use With AS 200.
Stainless Steel Ball Bearings
*Based on standard dimensions for channel
Std Pkg: 20 · Wt/100 pcs: 46 lbs.

Four Wheel Trolley

AS 2522 EG



Use With AS 200.
Stainless Steel Ball Bearings
*Based on standard dimensions for channel
Std Pkg: 10 · Wt/100 pcs: 110 lbs.

LEGEND:

GR: Powder Coated Supr-Green EG: Electro-Galvanized PG: Pre-Galvanized AL: Aluminum
HG: Hot Dipped Galvanized PL: Plain SS: Stainless Steel ZTC: Zinc Trivalent Chromium
Stainless Steel (SS), Zinc Trivalent Chromium (ZTC) and Hot Dipped Galvanized (HG) are specialty finishes.
Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.