

The C-4 Rigid Coupling is our standard coupling and is designed for rigid piping applications. The C-4 is specially designed to provide a rigid, locked-in pipe connection to meet the specific demands of rigid design steel pipe.

For Listings/Approval Details and Limitations, visit our website at www.asc-es.com or contact an ASC Engineered Solutions™ Sales Representative.



Material Specifications

Housing

Ductile Iron conforming to ASTM A536, Grade 65-45-12

Bolts

SAE J429, Grade 5, Zinc Electroplated (Standard)

Heavy Hex Nuts

ASTM A563, Grade A, Zinc Electroplated, Violet Dyed (Standard)

Coatings

Rust inhibiting paint Color: Orange (Standard) Hot Dipped Zinc Galvanized (Optional)

Lubrication

Standard Gruvlok Gruvlok Xtreme

Gasket Materials

Properties as designated in accordance with ASTM D2000

Pre-Lubricated Grade "E" EPDM, Type A

C-Style Gasket (Violet color code) -40°F to 150°F (Service Temperature Range) (-40°C to 66°C)

Recommended for wet and dry (oil free air) fire protection sprinkler systems. For freezing conditions, Gruvlok Xtreme Lubricant is required.

Grade "EP" EPDM Flush Gap Gasket

(Green color code) -40°F to 230°F (Service Temperature Range) (-40°C to 110°C)

Recommended for wet and dry (oil free air) fire protection sprinkler systems. For freezing conditions, Gruvlok Xtreme Lubricant is required.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	



Rigid Coupling Fig. C-4



Nominal	Pipe	Max. Working	Max. End	Range of Pine End	Coupling Dimensions			Coup	Approx.	
Size	U.D.	Pressure 🔺	Load	Separation	Х	Y	Z	Qty.	Size	Wt. Ea.
In./DN(mm)	In./mm	PSI/bar	Lbs./kN	In./mm	In./mm	In./mm	In./mm		In./mm	Lbs./kg
1	1.315	300	407	0-1/32	23/8	4	1 3⁄4	2	³ / ₈ x 2 ¹ / ₄	1.2
25	33.4	20.7	1.81	0-0.79	60	102	44		M10 x 57	0.5
1 1/4	1.660	300	649	0-1/32	25/8	41⁄4	1 23/32	2	³ / ₈ x 2 ¹ / ₄	1.4
32	42.2	20.7	2.89	0-0.79	67	108	44		M10 x 57	0.6
1 1/2	1.900	300	851	0-1/32	27/8	41/2	1 23/32	2	³ /8 x 2 ¹ /4	1.5
40	48.3	20.7	3.78	0-0.79	73	114	44		M10 x 57	0.7
2	2.375	300	1,329	0-1/32	3 11/32	5 ³ /16	1 23/32	2	³ / ₈ x 2 ¹ / ₄	1.7
50	60.3	20.7	5.91	0-0.79	85	132	44		M10 x 57	0.8
21/2	2.875	300	1,948	0-1/32	31/8	511/16	1 23/32	2	³ ∕8 x 2¹∕₂	1.9
65	73.0	20.7	8.66	0-0.79	98	144	44		M10 x 63	0.9
3	3.500	300	2,886	0-1/32	41/2	61⁄4	1 3⁄4	2	³ ∕8 X 3	2.4
80	88.9	20.7	12.84	0-0.79	114	159	44		M10 x 70	1.1
4	4.500	300	4,771	0-3/32	53/4	77/16	1 7/8	2	³ ∕8 X 3	3.5
100	114.3	20.7	21.22	0-2.38	146	189	48		M10 x 70	1.6
5	5.563	300	7,292	0-3/32	6 ¹³ /16	8 15/16	1 7/8	2	¹⁄₂ x 3	4.5
125	141.3	20.7	32.44	0-2.38	173	227	48		M12 x 70	2.0

Note:

Range of Pipe End Seperation values are for roll grooved pipe and may be doubled for cut groove pipe.

1. Working pressure and/or end load are total allowable, based on standard weight steel pipe, roll or cut grooved.

2. One time field test pressure may be increased to 1.5 times the figures listed above.

▲ – Working Pressure Ratings are for reference only and based on Sch. 10 and Sch. 40 pipe.

WARNING: For dry pipe systems and freezer applications lubrication of the gasket is required, Gruvlok Xtreme Lubricant is required.



asc-es.com

Building connections that last

SPF/Anvil® Rigid Couplings



Rigid Coupling Fig. C-4

(continued)



Nominal	Pipe	Max. Working	Max. End	Range of Pipe End	Range of Coupling Dimensions		Coupling Bolts		Approx.	
Size	0.D.	Pressure A	Load	Separation	Х	Y	Z	Qty.	Size	Wt. Ea.
In./DN(mm)	In./mm	PSI/bar	Lbs./kN	In./mm	In./mm	In./mm	In./mm		In./mm	Lbs./kg
б	6.625	300	10,341	0-3/32	71/8	101/16	1 15/16	2	¹⁄₂ x 3	5.4
150	168.3	20.7	46.00	0-2.38	200	256	49		M12 x 70	2.4
8	8.625	300	17,528	0-3/32	101/8	127/16	23/8	2	1⁄2 x 3	9.5
200	219.1	20.7	77.97	0-2.38	257	316	60		M12 x 70	4.3
10	10.750	300	27,229	0-3/32	13	16¾	25/8	2	⁷ ∕8 x 5	21.5
250	273.1	20.7	121.12	0-2.38	331	425	67		M22 x 125	9.8
12	12.750	300	38,303	0-3/32	153/8	19¼	25/8	2	⁷ ∕8 x 5 ½	27.4
300	323.9	20.7	170.38	0-2.38	391	489	67		M22 x 140	12.4

Note:

Range of Pipe End Seperation values are for roll grooved pipe and may be doubled for cut groove pipe.

1. Working pressure and/or end load are total allowable, based on standard weight steel pipe, roll or cut grooved.

2. One time field test pressure may be increased to 1.5 times the figures listed above.

▲ – Working Pressure Ratings are for reference only and based on Sch. 10 and Sch. 40 pipe.

WARNING: For dry pipe systems and freezer applications lubrication of the gasket is required, Gruvlok Xtreme Lubricant is required.



asc-es.com

Building connections that last



Fig. C-4 Rigid Coupling



before use.

WARNING Ensure system is drained and depressurized before installation or service.

Use appropriate personal protective equipment.



Failure to follow these instructions could result in serious personal injury and/or property damage.

Check pipe ends for proper grooved dimensions and to ensure that the pipe is free of indentations, projections, or other imperfections that would prevent proper sealing of the gasket.

1 Check and lubricate gasket

Check gasket to be sure it is compatible for the intended service. Apply a thin coating of Gruvlok lubricant to the exterior surface and sealing lips of the gasket. Some applications require lubrication of the entire gasket surface. Be careful that foreign particles do not adhere to lubricated surfaces. Pre-lubricated gaskets do not require lubrication.

Notice: Gruvlok Xtreme Lubricant must be applied when used in dry pipe systems or freezer applications.

2 Gasket installation

Slip the gasket over the pipe end making sure the gasket lip does not overhang the pipe end.

On couplings 10" and larger it may be easier to turn the gasket inside out then lubricate and slide the gasket over the pipe end as shown.

3 Alignment

After aligning the two pipe ends, pull

the gasket into position centering it between the grooves on each pipe. Gasket should not extend into the groove on either pipe.

On couplings 10" and larger, flip or roll the gasket into centered position.



4 Housings Remove one nut and bolt and loosen

the other nut. Place one housing over the gasket, making sure the housing keys fit into the pipe grooves. Swing the other housing over the gasket and into the grooves on both pipes, making sure the tongue and recess of each housing is properly mated. Reinsert the bolt and run-up both nuts finger tight.

5 Tighten nuts

Securely tighten nuts alternately and equally, keeping the gaps at the bolt pads evenly spaced.

Notice: Uneven tightening may cause the gasket to pinch. Gasket should not be visible between segments after bolts are tightened.











ANSI Specified Bolt Torque

Bolt Size	Wrench Size	Specified Bolt Torque*
ln.	ln.	FtLbs
3/8	¹¹ / ₁₆	30-45
1/2	7/8	80-100
5/8	1 ¹ / ₁₆	100-130
7/8	1 ⁷ / ₁₆	180-220

* Non-lubricated bolt torque.

6 Assembly is complete

Visually inspect the pipe joint to assure the coupling keys are fully engaged in the pipe grooves. The bolt pads are to have equal gaps on each side of the coupling.

Notice: Visually inspect both sides of the coupling to ensure gaps between bolt pads are evenly spaced and are parallel. Any deviations must be corrected before placing coupling into service.





asc-es.com

Building connections that last