


Building connections that last™





10 QVA

Unibody Carbon Steel Ball Valves Datasheet



Unibody Carbon Steel Ball Valves

10 QVA



Features

- AISI 1017 Carbon Steel Bodies and Tailpieces
- 2000 psi CWP Rating on All Sizes
- 150 PSIG Saturated Steam Rating
- All Models are NACE MR-01-75 Compliant
- 316 Stainless Steel Ball and Stem Available
- "Live Loaded" Stem Packing Design
- "Tamperproof" Locking Handles Available in Carbon and Stainless Steel


Ratings

2000 PSIG @100°F

All Sizes - 150 PSIG Saturated Steam




Materials of Construction

Part	Description	Standard Material	Optional Material(s)
1	Body	AISI Gr. 1017	
2	Tailpiece	AISI Gr. 1017	
3	Ball	ASTM A276 Gr. 304SS	ASTM A276 Gr. 316SS
4	Stem	AISI 1045 Carbon Steel	ASTM A276 Gr. 316SS
5	Packing Nut	Carbon Steel-Plated	
6	Seats (2)	R-PTFE	
7	Packing	R-PTFE	
8	Washer	ASTM A276 Gr. 304SS	
9	Thrust Washer (2)	TFE	
10	Belleville Washer (2)	Carbon Steel-HT	
11	Handle Assy	Carbon Steel-Plated	304 Stainless Steel
12	Handle Nut	Carbon Steel-Plated	304 Stainless Steel



Unibody Carbon Steel Ball Valves

10 QVA



Dimensions, Weights, Cv Factors & Maximum Operating Torque

Size	A	B	C	D	E	Weight Lbs.	CV	Max Torque
1/4-3/8"	0.35	1.1	2.22	2.21	4.17	0.7	4	60 IN-LB
1/2"	0.35	1.1	2.19	2.21	4.17	0.6	4	60 IN-LB
3/4"	0.47	1.31	2.63	2.32	4.17	0.8	8	75 IN-LB
1"	0.62	1.58	3.15	2.68	5.83	1.7	14	150 IN-LB
1-1/4"	0.81	1.81	3.62	2.87	5.83	2.5	19	180 IN-LB
1-1/2"	1.00	2.00	4.00	3.11	7.01	3.7	33	250 IN-LB
2"	1.25	2.25	4.5	3.39	7.24	5.7	51	350 IN-LB

Numbering System How to order 10 QVA

10	D	C	C	R	R	LH	TT	100
Series	Port Size	Body Material	Ball/Stem Material	Seat Material	Seal Material	Handle Type	Ends	Size
10 Unibody (Barstock)	D Double Reduced	C Carbon	C Plated Carbon	R R-PTFE	R R-PTFE	LH CS Lever	TT FNPT	025 1/4"
			S 316 Stainless			LL CS Latch Lock		038 3/8"
			SH Stainless Lever			050 1/2"		
			SL Stainless Latch Lock			075 3/4"		
							100 1"	
								125 1-1/4"
								150 1-1/2"
								200 2"

About ASC Engineered Solutions

ASC Engineered Solutions is defined by quality—in its products, services and support. With more than 1,400 employees, the company's portfolio of precision-engineered piping support, valves and connections provides products to more than 4,000 customers across industries, such as mechanical, industrial, fire protection, oil and gas, and commercial and residential construction. Its portfolio of leading brands includes ABZ Valve®, AFCON®, Anvil®, Anvil EPS, Anvil Services, Basic-PSA, Beck®, Catawissa, Cooplet®, FlexHead®, FPPI®, Grevlok®, J.B. Smith, Merit®, North Alabama Pipe, Quadrant®, SCI®, Sharpe®, SlideLOK®, SPF® and SprinkFLEX®. With headquarters in Commerce, CA, and Exeter, NH, ASC also has ISO 9001:2015 certified production facilities in PA, TN, IL, TX, AL, LA, KS, and RI.



asc-es.com

Building connections that last™

FC-DS-10 QVA-v02 20220112

