


Domestic Red Brass Nipples Fig. BRASSNI



Standards & Specifications

Specifications

All Trenton Brass and Chrome Plated Brass Nipples are manufactured to the exacting standards of ASTM B-687 (Rev. 96) Standard nipple threads are NPT National (American) Pipe Taper threads. In addition to the standard NPT threads, nipples are available in a variety of thread forms. See NPT Thread Data.

Sizes / Diameters

Diameters from 1/8" thru 6" in regular (Schedule 40) and 1/8" thru 4 in Extra Strong (Schedule 80)

Lengths

Pipe and therefore nipples are available in virtually ANY length but most pipes stocked in 12 ft lengths.

Tempers

All are available in General Purpose Drawn Temper (H58 temper) and most are also available in Annealed (O61 temper). (Unless specified otherwise, H-58 temper will be supplied).

Dimensions

Size	Length of Close	Close	1-1/2	2	2-1/2	3	3-1/2	4	4-1/2	5	5-1/2	6	7	8	9	10	11	12
1/8"	3/4"	1	3	4	5	6	7	8	9	10	12	13	15	17	19	21	24	26
1/4"	7/8"	2	5	7	9	11	13	14	14	16	18	20	22	26	33	37	41	44
3/8"	1	4	6	9	12	14	16	19	21	24	27	29	34	39	44	48	53	58
1/2"	1-1/8"	6	8	12	15	18	22	26	30	33	36	39	46	53	61	68	75	82
3/4"	1-3/8"	10	12	15	20	25	30	35	40	45	50	56	66	76	86	95	105	115
1"	1-1/2"	15		21	28	36	43	52	58	65	71	77	91	105	118	132	146	160
1-1/4"	1-5/8"	23		30	41	52	59	66	75	84	94	105	125	146	166	187	207	277
1-1/2"	1-3/4"	32		38	48	60	70	83	94	105	118	131	155	180	204	228	252	277
2"	2	50		75	90	103	118	134	150	165	180	212	244	276	308	340	372	
2-1/2"	2-1/2"	90			115	140	165	190	215	240	260	310	360	410	460	510	560	
3"	2-5/8"	135			170	205	240	280	315	350	385	455	525	595	665	735	805	
3-1/2"	-	200					330	390	425	455	490	580	670	760	850	935	1025	
4"	2-7/8"	230					360	410	455	505	550	645	740	835	930	1025	1120	



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	