

## Reducing 90° Elbow (Groove x Thread) Fig. SE-5



### Material Specifications

#### Cast Fittings

Ductile Iron conforming to ASTM A536, Grade 65-45-12

#### Coatings

Rust inhibiting paint

Color: Black

Other available options

Example: RAL3000 or RAL9000 Series




- SE-5 ductile iron fittings are grooved on the large end and reduced size female NPT threaded on the small end. The SE-5 fittings are ideal for all types of applications where transition from grooved to female thread is required.
- SE-5 fittings allow for convenient connection of drains, vents, pressure gauges as well as direct connection of an end of line sprinkler head.
- All sizes are UL, ULC listed and FM approved for 300 PSI working pressure.

For Listings/Approval Details and Limitations, visit our website at [www.asc-es.com](http://www.asc-es.com) or contact an ASC Engineered Solutions™ Sales Representative.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

## Reducing 90° Elbow (Groove x Thread) Fig. SE-5



Nominal Size	O.D.	Max. Wk. Pressure	X	Y	Approx. Wt. Ea.
In./DN(mm)	In./mm	PSI/bar	In./mm	In./mm	Lbs./kg
1 1/4 x 1/2 32 x 15	1.660 42.2	300 20.7	1 3/4 44	1 3/8 35	0.5 0.3
1 1/4 x 3/4 32 x 20	1.660 42.2	300 20.7	1 7/8 48	1 3/8 35	0.5 0.3
1 1/4 x 1 32 x 25	1.660 42.2	300 20.7	2 51	1 1/2 38	0.6 0.3
1 1/2 x 1/2 40 x 15	1.900 48.3	300 20.7	1 3/4 44	1 3/8 35	0.6 0.3
1 1/2 x 3/4 40 x 20	1.900 48.3	300 20.7	1 7/8 48	1 3/8 35	0.7 0.3
1 1/2 x 1 40 x 25	1.900 48.3	300 20.7	2 51	1 1/2 38	0.8 0.4
2 x 1/2 50 x 15	2.375 60.3	300 20.7	1 3/4 44	1 5/8 41	0.8 0.4
2 x 3/4 50 x 20	2.375 60.3	300 20.7	1 7/8 48	1 5/8 41	0.9 0.4
2 x 1 50 x 25	2.375 60.3	300 20.7	2 51	1 3/4 44	1.0 0.5
2 1/2 x 1/2 65 x 15	2.875 73.0	300 20.7	1 3/4 44	1 13/16 46	1.2 0.5
2 1/2 x 3/4 65 x 20	2.875 73.0	300 20.7	1 7/8 48	1 13/16 46	1.3 0.6
2 1/2 x 1 65 x 25	2.875 73.0	300 20.7	2 51	1 15/16 49	1.5 0.7
3 x 3/4 80 x 20	3.500 88.9	300 20.7	2 1/16 52	2 3/8 60	2.2 1.0
3 x 1 80 x 25	3.500 88.9	300 20.7	2 1/16 52	2 1/2 64	2.5 1.1



asc-es.com

Building connections that last™