

Flange Nipple
Fig. F-2



Material Specifications

Flange

Class 150 Carbon Steel Raised Face Flange

Fabricated Fittings

1"-10" Carbon Steel, Schedule 40, conforming to ASTM A53, Grade B

12" and above Carbon Steel, Standard Wall, conforming to ASTM A53, Grade B

Coatings

Rust inhibiting paint

Color: Orange or Black (standard)

Hot Dipped Zinc Galvanized

conforming to ASTM A153 (optional)


Other available options

(Example: RAL3000 or RAL9000 Series)

Nominal Size	O.D.	End to End	Approx. Wt. Ea.	Nominal Size	O.D.	End to End	Approx. Wt. Ea.
In./DN(mm)	In./mm	In./mm	Lbs./kg	In./DN(mm)	In./mm	In./mm	Lbs./kg
2	2.375	4	6.2	6	6.625	6	50.0
50	60.3	102	2.8	150	168.3	152	22.7
2½	2.875	4	9.9	8	8.625	6	60.0
65	73.0	102	4.5	200	219.1	152	27.2
3	3.500	4	11.4	10	10.750	8	60.0
80	88.9	102	5.0	250	273.1	203	27.2
4	4.500	6	47.0	12	12.750	8	91.0
100	114.3	152	21.3	300	323.9	203	41.3
5	5.563	6	40.0				
125	141.3	152	18.1				

Note:

Larger sizes available upon request, contact an ASC Engineered Solutions™ Representative.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	