



Medium Duty Pipe Hanger Support Series with Top Support HBS-PH 36" Medium Duty Pipe Hanger Support, PG, HG



The HBS-PH Series is designed specifically for supporting piping.

Specifications: Fixed Width & Height. All hardware required for assembly is included.

Base Material: 100% recycled rubber, UV resistant

Crossbeams: 2-7/16" H-122 Channel or 3-3/4" H-112 Channel

HBS-PH 36" Medium Duty Pipe Hanger Support Series with H-122 PG Top Support

Model No.	Height	Strut Width	Base Width	Base Length	No. of Bases	Weight (Lbs)	Uniform Load Capacity (Lbs)*
HBS-PH-36-36-H-122-PG		36" (914 mm)	39 ³ / ₈ " (1000 mm)			63	2,190*
HBS-PH-36-48-H-122-PG	36"	48" (1219 mm)	51 ³ / ₈ " (1305 mm)	36"	6	66	1,635*
HBS-PH-36-60-H-122-PG	(914 mm)	60" (1524 mm)	63 ³ / ₈ " (1610 mm)	(914 mm)		68	1,305*
HBS-PH-36-72-H-122-PG		72" (1829 mm)	75 ³ / ₈ " (1915 mm)			71	1,080*

*This load is only for the capacity of the components in this assembly with the pipe hangers located at a distance 1/4 from each end of the top channel. For pipe hangers located 1/3 from each end, multiply uniform load by .75. For any other loading scenario, please consult the appropriate engineer. Please consult Roofing manufacturer or engineer for roof load capacity.
Torque Setting - All load capacities stated herein are based on the use of 1/2" channel nuts tightened to 50 ft-lbs.

HBS-PH 36" Medium Duty Pipe Hanger Support Series with H-112 PG Top Support

Model No.	Height	Strut Width	Base Width	Base Length	No. of Bases	Weight (Lbs)	Uniform Load Capacity (Lbs)*
HBS-PH-36-36-H-112-PG		36" (914 mm)	39 ³ / ₈ " (1000 mm)			65	3,505*
HBS-PH-36-48-H-112-PG	36"	48" (1219 mm)	51 ³ / ₈ " (1305 mm)	36"	6	68	2,620*
HBS-PH-36-60-H-112-PG	(914 mm)	60" (1524 mm)	63 ³ / ₈ " (1610 mm)	(914 mm)		71	2,090*
HBS-PH-36-72-H-112-PG		72" (1829 mm)	75 ³ / ₈ " (1915 mm)			74	1,735*

*This load is only for the capacity of the components in this assembly with the pipe hangers located at a distance 1/4 from each end of the top channel. For pipe hangers located 1/3 from each end, multiply uniform load by .75. For any other loading scenario, please consult the appropriate engineer. Please consult Roofing manufacturer or engineer for roof load capacity.
Torque Setting - All load capacities stated herein are based on the use of 1/2" channel nuts tightened to 50 ft-lbs.

LEGEND:

PG: Pre-Galvanized **HG:** Hot Dipped Galvanized
Pricing is located in the ASC Engineered Solutions™ H-Block price book.

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	