


HARD-LID CEILING GRID WITH RECESSED SPRINKLER




HOSE HEIGHT CLEARANCE CHART


MINIMUM BEND RADIUS "R"	MINIMUM "B"	MINIMUM "C"
2in [50mm]	2 3/4" [70mm]	9 9/16" [243mm]
3in [76mm]	3 3/4" [95mm]	10 9/16" [268mm]
4in [101mm]	4 3/4" [120mm]	11 9/16" [294mm]
5in [127mm]	5 3/4" [146mm]	12 9/16" [319mm]
6in [152mm]	6 3/4" [171mm]	13 9/16" [344mm]
7in [178mm]	7 3/4" [197mm]	14 9/16" [370mm]

NOTE: CLEARANCE WILL SLIGHTLY VARY BASED ON "C" HEIGHT INSTALLATION

HARD-LID CEILING GRID WITH RECESSED SPRINKLER WITH 90° ELBOW (LONG)



HARD-LID CEILING GRID WITH CONCEALED SPRINKLER WITH 90° ELBOW (LONG)



NOTES:

- DIMENSION "A", VARIATION OF SPRINKLER HEAD TYPE AND ASSEMBLY, CEILING GRIDS, AND HOSE MAY VARY OVERALL HEIGHT CLEARANCE AS SHOWN HERE.
- FOR EASE OF TILE INSTALLATION, USE LARGEST HOLE RECOMMENDED BY SPRINKLER HEAD MANUFACTURE.

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES FRACTIONAL ±1/2 ANGULAR ±14° BEHD ±14° 1 PLACE DECIMAL [0] ±0.020 2 PLACE DECIMAL [XX] ±0.010 3 PLACE DECIMAL [XXX] ±0.005	NAME: Admin DATE: 12/07/16	56 Lowland Street, Holliston MA 01746 WWW.FLEXHEAD.COM 1-800-829-6975	
DRAWN BY: Admin CHECKED BY: ENG APPR: MFG APPR: Q.A. APPR:	DATE: 12/07/16	TITLE: MPT BRACKET STUD INSTALLATION CLEARANCE CUST/SUP NAME: CUST/SUP PART #:	REV: B
INTERPRET GEOMETRIC TOLERANCING PER: MATERIAL: FINISH:	SCALE: 1:8	WEIGHT: SHEET 1 OF 1	