

Oil Country Fittings Pup Joints

Material Options

Tubing per API 5CT, Grades J-55, N-80 & L-80

Finish Options – External Surfaces


Rust Inhibiting Paint per API 5CT

- J55 – Green
- J80 – Red with Green Stripe
- L80 – Red with Brown Stripe

Finish Options – Internal Surfaces

- Scotchkote 134
- Corvel 1660

Pup joints are available in solid and perforated tubing.



Size	Pup Joints								Couplings					
	D1		D2		D3		t		L1		D4		L2	
in	in	mm	in	mm	in	mm	in	mm	Ft	m	in	mm	in	mm
2" 8RD EUE x 2" 8RD EUE	1.99	51	2.59	66	2.38	61	0.19	5	2, 3, 4, 6, 8, 10, 12	0.6, 0.9, 1.2, 1.8, 2.4, 3.0, 3.7	3.06	78	4.88	124
2½" 8RD EUE x 2½" 8RD EUE	2.44	62	3.09	79	2.88	73	0.22	6			3.67	93	5.25	133

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	