


WARDFlex® Tubing & Components Female Mechanical Joints



The 3/8" through 1 1/4" WARDFlex® tubing is terminated using the patented, STEPSAVER double seal fitting. The 1 1/2" and 2" tubing utilize the WARDFlex® traditional gasketed fitting design. Only fittings designed and listed for use with the WARDFlex® and WARDFlex® MAX CSST Piping Systems shall be used when connecting to the flexible piping.

Features

- Approved for concealed use
- One corrugation crush seal
- Reusable
- 3/8" through 1 1/4" patented STEPSAVER fittings
 - Primary metal to metal seal
 - Secondary gasket seal
- 1 1/2" and 2" fittings
 - Reliable gasket seal

Components

- Female NPT Body
- Retainer Ring
- Nut
- Gasket

Listings

- CSA: File # 112940_0_000
- IAPMO: File # 3353
- ICC: Report # ESR-1879

Technical Data

General

Certified Operating Pressure
25 psi

Materials

Body, Retainer Ring, & Nut
Brass

Gasket
Composite Fiber



Dimensions

Price Sheet Item #	CSST Size	NPT Size	Assembled Length	Nut Hex	Fitting Hex	Maximum Tightening Torque (ft/lbs)	Approximate Weight (lbs)
250	3/8"	1/2"	1.484"	1 1/16"	1 1/16"	50	0.28
251	1/2"	1/2"	1.482"	1 3/16"	1 1/16"	50	0.28
258	1/2"	3/8"	1.482"	1 3/16"	1 1/16"	50	0.32
252	3/4"	3/4"	1.658"	1 1/2"	1 1/2"	120	0.60
442	3/4"	1/2"	1.658"	1 1/2"	1 1/2"	120	0.67
253	1"	3/4"	1.772"	1 3/4"	1 3/4"	160	0.94
254	1"	1"	1.772"	1 3/4"	1 3/4"	160	0.79

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	