


WARDFlex® Tubing & Components Female Outdoor Termination Fitting



The 3/8" through 1 1/4" WARDFlex® tubing is terminated using the patented, STEPSAVER double seal fitting. The 1 1/2" and 2" tubing utilize the WARDFlex® traditional gasketed fitting design. Only fittings designed and listed for use with the WARDFlex® and WARDFlex® MAX CSST Piping Systems shall be used when connecting to the flexible piping.

Features

- Provides fixed point termination on wall or floor
- One corrugation crush seal
- Reusable
- 3/8" through 1 1/4" patented STEPSAVER fittings
 - Primary metal to metal seal
 - Secondary gasket seal

Components

- Female NPT Body
- Retainer Ring
- Termination Nut
- Gasket
- Termination Fitting Base Plate with 2 screws
- Outdoor fittings are supplied with o-rings

Listings

- CSA: File # 112940_0_000
- IAPMO: File # 3353
- ICC: Report # ESR-1879

Technical Data

General

Certified Operating Pressure
25 psi

Materials

Body, Retainer Ring
Brass

Termination Nut
Malleable Iron

Gasket
Composite Fiber

Base Plate
Steel



Dimensions

Price Sheet Item #	CSST Size	NPT Size	Nut Hex	Fitting Hex	Width of Termination Nut	Assembled Length	Maximum Tightening Torque (ft/lbs)	Approximate Weight (lbs)
290	3/8"	1/2"	1.10"	1 1/16"	2.60"	1.636"	50	0.79
291	1/2"	1/2"	1.22"	1 1/16"	2.60"	1.674"	50	0.80
292	3/4"	3/4"	1.54"	1 1/2"	3.00"	1.850"	120	1.17
294	1"	1"	1.77"	1 3/4"	3.46"	1.972"	160	1.50

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	