


WARDFlex® Tubing & Components Floor Flanged Termination Fitting



The 3/8" through 1 1/4" WARDFlex® tubing is terminated using the patented, STEPSAVER double seal fitting. The 1 1/2" and 2" tubing utilize the WARDFlex® traditional gasketed fitting design. Only fittings designed and listed for use with the WARDFlex® and WARDFlex® MAX CSST Piping Systems shall be used when connecting to the flexible piping.

Features

- Provides fixed termination on floor
- Approved for concealed use
- One corrugation crush seal
- Reusable
- 3/8" through 1 1/4" patented STEPSAVER fittings
- Primary metal to metal seal
- Secondary gasket seal
- 1 1/2" and 2" fittings
- Reliable gasket seal

Components

- Male NPT Body
- Retainer Ring
- Adapter Nut
- Gasket
- Floor Flange

Listings

- CSA: File # 112940_0_000
- IAPMO: File # 3353
- ICC: Report # ESR-1879

Technical Data

General

Certified Operating Pressure
25 psi

Materials

Body, Retainer Ring & Adapter Nut
Brass

Flange Nut
Malleable Iron

Gasket
Composite Fiber



Dimensions

Price Sheet Item #	CSST Size	NPT Size	Nut Hex	Fitting Hex	Flange Diameter	Maximum Tightening Torque (ft/lbs)	Approximate Weight (lbs)
300	3/8"	1/2"	1 3/16"	1 1/16"	3.25"	50	1.00
301	1/2"	1/2"	1 3/16"	1 1/16"	3.25"	50	0.90
302	3/4"	3/4"	1 1/2"	1 1/2"	3.88"	120	1.56
304	1"	1"	1 3/4"	1 3/4"	3.88"	160	1.72

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	