


WARDFlex® Tubing & Components Male Mechanical Joints



The 3/8" through 1 1/4" WARDFlex® tubing is terminated using the patented, STEPSAVER double seal fitting. The 1 1/2" and 2" tubing utilize the WARDFlex® traditional gasketed fitting design. Only fittings designed and listed for use with the WARDFlex® and WARDFlex® MAX CSST Piping Systems shall be used when connecting to the flexible piping.

Features

- Approved for concealed use
- One corrugation crush seal
- Reusable
- 3/8" through 1 1/4" patented STEPSAVER fittings
 - Primary metal to metal seal
 - Secondary gasket seal
- 1 1/2" and 2" fittings
 - Reliable gasket seal

Components

- Male NPT Body
- Retainer Ring
- Nut
- Gasket

Listings

- CSA: File # 112940_0_000
- IAPMO: File # 3353
- ICC: Report # ESR-1879

Technical Data

General

Certified Operating Pressure
25 psi

Materials

Body, Retainer Ring, & Nut
Brass

Gasket
Composite Fiber



Dimensions

Price Sheet Item #	CSST Size	NPT Size	Assembled Length	Nut Hex	Fitting Hex	Maximum Tightening Torque (ft/lbs)	Approximate Weight (lbs)
201	3/8"	1/2"	1.679"	1 1/16"	1 1/16"	50	0.31
211	3/8"	3/8"	1.679"	1 1/16"	1 1/16"	50	0.26
202	1/2"	1/2"	1.642"	1 3/16"	1 3/16"	50	0.28
212	1/2"	3/8"	1.642"	1 3/16"	1 3/16"	50	0.24
209	3/4"	1/2"	1.723"	1 1/2"	1 1/2"	120	0.47
203	3/4"	3/4"	1.763"	1 1/2"	1 1/2"	120	0.47
204	1"	3/4"	1.837"	1 3/4"	1 3/4"	160	0.65
205	1"	1"	1.937"	1 3/4"	1 3/4"	160	0.66
206	1 1/4"	1 1/4"	2.197"	2 1/4"	2 1/4"	200	1.31
207	1 1/2"	1 1/2"	2.642"	3"	3"	200	2.90
208	2"	2"	2.945"	3 1/2"	3 1/2"	200	3.93

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	