

WARDFlex® Tubing & Components Mechanical Tees



The 3/8" through 1 1/4" WARDFlex® tubing is terminated using the patented, STEPSAVER double seal fitting. The 1 1/2" and 2" tubing utilize the WARDFlex® traditional gasketed fitting design. Only fittings designed and listed for use with the WARDFlex® and WARDFlex® MAX CSST Piping Systems shall be used when connecting to the flexible piping.

Features

- Approved for concealed use
- One corrugation crush seal
- Reusable
- 1 1/2" and 2" fittings
 - Reliable gasket seal
- 3/8" through 1 1/4" patented STEPSAVER fittings
 - Primary metal to metal seal
 - Secondary gasket seal

Components

- Tee Body
- Retainer Ring (3)
- Nut (3)
- Gasket (3)

Listings

- CSA: File # 112940_0_000
- IAPMO: File # 3353
- ICC: Report # ESR-1879

Technical Data

General

Certified Operating Pressure
25 psi

Materials

1/2" - 1 1/4" Body, Retainer Ring & Nut
Brass

1 1/2" - 2" Body
Malleable Iron

Gasket
Composite Fiber



Dimensions

Price Sheet Item #	CSST Size A	Nut Hex A	CSST Size B	Nut Hex B	CSST Size C	Nut Hex C	Assembled Length	Approximate Weight (lbs)
351	1/2"	1 3/16"	1/2"	1 3/16"	1/2"	1 3/16"	2.894"	1.30
362	1/2"	1 3/16"	1/2"	1 3/16"	3/8"	1 1/16"	2.894"	1.29
363	1/2"	1 3/16"	3/8"	1 1/16"	3/8"	1 1/16"	2.894"	1.27
365	3/4"	1 1/2"	3/4"	1 1/2"	1/2"	1 3/16"	3.31"	1.43
366	3/4"	1 1/2"	1/2"	1 3/16"	1/2"	1 3/16"	3.31"	1.34
352	3/4"	1 1/2"	3/4"	1 1/2"	3/4"	1 1/2"	3.31"	1.51
353	1"	1 3/4"	1"	1 3/4"	1"	1 3/4"	3.73"	2.24
358	1"	1 3/4"	1"	1 3/4"	1/2"	1 3/16"	3.73"	2.37
357	1"	1 3/4"	1"	1 3/4"	3/4"	1 1/2"	3.73"	2.20
360	1"	1 3/4"	3/4"	1 1/2"	3/4"	1 1/2"	3.73"	2.29
359	1"	1 3/4"	3/4"	1 1/2"	1/2"	1 3/16"	3.73"	2.26
354	1 1/4"	2 1/4"	1 1/4"	2 1/4"	1 1/4"	2 1/4"	5.35"	3.95
355	1 1/2"	3"	1 1/2"	3"	1 1/2"	3"	6.38"	7.94
356	2"	3 1/2"	2"	3 1/2"	2"	3 1/2"	7.40"	11.41

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	