

Sharpe® Series 3483

Forged Gate Valve Datasheet





Forged Gate Valve Sharpe® Series 3483





Design Features

- Class 800
- Socket weld ends forged steel or 316L stainless steel
- Threaded ends forged steel or 316L stainless steel
- Bolted bonnet
- Rising stem
- NACE MR-0175

Applicable Standards

• Basic Design: API 602 (9th Edition)

Socket Weld: ASME B16.11

• Threaded: ASME B1.20.1

Test: API 598

Technical Information

Size	C_{V}	Weight (Lbs.)		
1/4	3	4.5		
3/8	5	4.6		
1/2	7	4.4		
3/4	14	4.9		
1	30	7.8		
1-1/4	85	11.8		
1-1/2	100	13.5		
2	160	21.0		

Temperature °F	316L Pressure psi	Forged Steel Pressure psi
-20 to 100	1600	1975
200	1365	1810
300	1215	1745
400	1120	1690
500	1050	1610
600	990	1515
650	975	1465
700	960	1415
750	940	1350
800	920	1100
850	900	-




asc-es.com

Building connections that last™



Forged Gate Valve Sharpe® Series 3483





Parts & Materials

No.	Part Name	Qty.	Material
1	Body	1	316L Stainless Steel ASTM A182 or Forged Steel ASTM A105N
2	Disc	1	316 Stainless Steel or 410 Stainless Steel*
3	Seat Ring	2	316 Stainless Steel or 410 Stainless Steel*
За	Seat	1	Stellite
4	Stem	1	316 Stainless Steel or 410 Stainless Steel*
5	Gasket	1	316 + Graphite or 304 + Graphite*
6	Bonnet	1	316L Stainless Steel or Carbon Steel ASTM A105N*
7	Packing	_1_	Graphite
8	Packing Flange	_1_	316 Stainless Steel or 410 Stainless Steel*
9	Gland Flange	1	304 Stainless Steel or Carbon Steel ASTM A105N*
10	Gland Studs	2	B8M Steel or 410 Stainless Steel*
11	Gland Nut	2	Gr8M Steel or B7M*
12	Hand Wheel	1	Carbon Steel
13	Hand Wheel Nut	1	Carbon Steel
14	Body Bolt	1	B8M Steel or B7M Steel ASTM A193*
15	Name Plate	1	Aluminum

Note:

*Used on Carbon Steel Valves

Dimensions (Inches)

Size	Α	В	С	D	Е	F
1/4	3.11	5.90	0.56	0.24	0.39	0.40
3/8	3.11	6.10	0.69	0.28	0.39	0.43
1/2	3.11	6.30	0.85	0.39	0.39	0.54
3/4	3.58	6.30	1.07	0.51	0.51	0.55
1	4.37	7.20	1.33	0.71	0.51	0.69
1-1/4	4.72	9.06	1.68	0.94	0.51	0.71
1-1/2	4.72	9.50	1.92	1.14	0.51	0.72
2	5.51	11.14	2.41	1.44	0.63	0.76



Forged Gate Valve

Sharpe® Series 3483



How to order Series 3483

Example: A 1" forged ASTM A182 316L stainless steel gate valve, Trim 12 with threaded end connections, is: **13483-6-TE**.

1	3483	-	6	_	TE		
Size (inch)	Series	Body Material			End Connections		
1/4	3483	4	Forged Steel ASTM A105N	TE	Threaded		
3%	(Class 800)	4	(Trim 8)	SW	Socket Weld		
1/2		6	Stainless Steel ASTM A182 Forged 316L				
3/4			(Trim 12)				
1							
1-1/4							
1-1⁄2							
2							

Note:

Responsibility for proper selection, use and maintenance of any product remains solely with the purchaser and end user. We reserve the right to modify or improve the designs or specifications of any product at any time without notice.



About ASC Engineered Solutions

ASC Engineered Solutions is defined by quality—in its products, services and support. With more than 1,400 employees, the company's portfolio of precision-engineered piping support, valves and connections provides products to more than 4,000 customers across industries, such as mechanical, industrial, fire protection, oil and gas, and commercial and residential construction. Its portfolio of leading brands includes ABZ Valve®, AFCON®, Anvil®, Anvil EPS, Anvil Services, Basic-PSA, Beck®, Catawissa, Cooplet®, FlexHead®, FPPI®, Gruvlok®, J.B. Smith, Merit®, North Alabama Pipe, Quadrant®, SCI®, Sharpe®, SlideLOK®, SPF® and SprinkFLEX®. With headquarters in Commerce, CA, and Exeter, NH, ASC also has ISO 9001:2015 certified production facilities in PA, TN, IL, TX, AL, LA, KS, and RI.







asc-es.com

Building connections that last™

