

WARDFlex® Tubing & Components Female Mechanical Tees

Components

- Female Tee Body
- Retainer Ring (2)
- Nut (2)
- Gasket (2)

Listings

- CSA: File # 112940_0_000
- IAPMO: File # 3353
- ICC: Report # ESR-1879

Technical Data

General


Certified Operating Pressure
25 psi

Materials

½"– 1 ¼" Body, Retainer Ring, & Nut
Brass

1 ½"– 2" Body
Malleable Iron

Gasket
Composite Fiber



The ¾" through 1 ¼" WARDFlex® tubing is terminated using the patented, STEPSAVER double seal fitting. The 1 ½" and 2" tubing utilize the WARDFlex® traditional gasketed fitting design. Only fittings designed and listed for use with the WARDFlex® and WARDFlex® MAX CSST Piping Systems shall be used when connecting to the flexible piping.

Features

- Approved for concealed use
- One corrugation crush seal
- Reusable
- 1 ½" and 2" fittings
 - Reliable gasket seal
- ¾" through 1 ¼" patented STEPSAVER fittings
 - Primary metal to metal seal
 - Secondary gasket seal

Dimensions

| Price Sheet Item # | CSST Size A | Nut Hex A | CSST Size B | Nut Hex B | NPT Size | Assembled Length | Approximate Weight (lbs) |
|--------------------|-------------|-----------|-------------|-----------|----------|------------------|--------------------------|
| 401 | ½" | 1 ¾" | ½" | 1 ¾" | ½" | 3.104" | 1.22 |
| 402 | ¾" | 1 ½" | ¾" | 1 ½" | ½" | 3.31" | 1.49 |
| 403 | ¾" | 1 ½" | ¾" | 1 ½" | ¾" | 3.31" | 1.36 |
| 408 | 1" | 1 ¾" | 1" | 1 ¾" | ¾" | 3.73" | 2.13 |
| 413 | 1" | 1 ¾" | 1" | 1 ¾" | 1" | 3.73" | 1.98 |
| 405 | 1 ¼" | 2 ¼" | 1 ¼" | 2 ¼" | 1 ¼" | 5.35" | 3.95 |
| 407 | 1 ½" | 3" | 1 ½" | 3" | 1 ½" | 6.38" | 8.08 |
| 409 | 2" | 3 ½" | 2" | 3 ½" | 2" | 7.40" | 11.02 |

| PROJECT INFORMATION | APPROVAL STAMP |
|---------------------|-------------------|
| Project: | Approved |
| Address: | Approved as noted |
| Contractor: | Not approved |
| Engineer: | Remarks: |
| Submittal Date: | |
| Notes 1: | |
| Notes 2: | |